# **Portable Popup Bar Mini**

#### PBFM902-B

The Portable Popup Bar is a portable, wheeled sampling and serving station perfect for any event. The pre-assembled aluminum frame comes together by unfolding the legs, and inserting the interior shelf panels. Fully-customized graphics and printed top will win visitors over as you provide an effortless serving experience.



### We are continually improving and modifying our product range and reserve the right to vary the specifications without prior notice. All dimensions and weights quoted are approximate and we accept no responsibility for variance. E&OE. See Graphic Templates for graphic bleed specifications.

#### features and benefits:

- Portable, pre-assembled aluminum frame
- Zipper-enclosed storage space
- Printable graphics available
- Locking wheel casters

- Kit includes frame, two shelfs, and a carry bag
- 1 year hardware warranty against manufacturer defects

Shipping

Packing case(s):


#### dimensions:

Assembled unit:

Hardware

23.94" w x 36.63"h x 20"d 609mm(w) x 931mm(h) x 508mm(d) Approximate weight: 18 lbs / 9 kg	1 Carry bag  Shipping dimensions: 26"l x 22"h x 7"d 661mm(l) x 559mm(h) x 178mm(d)  Approximate total shipping weight: 22 lbs / 10 kg
Graphic	additional information:
Refer to related graphic template for more information.  Visit: www.exhibitors-handbook.com/ graphic-templates	Graphic material: Oxford  Shelfs are shipped inside the Popup Bar on the bottom level.  When included in a larger kit, a different packaging solution will be listed to accommodate all contents of the kit. Individual packaging no longer provided.  Internal Shelf Weight Capacity: 19 lbs. Counter Top Weight Capacity: 25 lbs.

# **Included In Your Kit**



# **Kit Assembly**

### **Step by Step**


Step 1.
Unfold and lock legs.





**Step 2.**Unzip and insert shelfs.





Step 3.

Zip door to close or roll up hook and loop fastener to stay open.

If graphics have been purchased move on to step 4, otherwise Set-up is complete.





### Step 4.

Apply graphcis by pressing the sides of the graphics onto the counter, making sure the hook and loop fastener bands are aligned with one another.

Setup is complete.



